

Flat suction cup (round)

SUF 25 SI-CO-55 G1/8-IG




Art.-Nr.: 10.01.01.14144



SUF 25 SI-CO-55 G1/8-IG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data SUF 25 SI-CO-55 G1/8-IG

Technical data

Attribute	Value
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55.0 Shore A
Size	25.00
Vacuum connection	G1/8"-F

Design data

Attribute	Value
Height H	25.20 mm
Nominal diameter dn	4.10 mm
Thread G1	G1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	2.5 mm
Diameter Ds	25.0 mm
Diameter Dmax(S)	28.2 mm



WWW.SCHMALZ.COM/10.01.01.14144

Art.-Nr.: 10.01.01.14144

**Technical data**

Attribute	Value
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	25.0 mm
Pull-off force	23.00 N
Suction force (-600mbar)	23.00 N
Weight	10.50 g
Volume	0.900 cm ³
Size	25.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14144

**Ordering Data Spare Parts 10.01.01.14144**

Typ		Item number
Schmalz-Connector	SC 040 G1/8-IG	10.01.06.02482
Flat suction cup (round)	SUF 25 SI-CO-55 SC040	10.01.01.14039

