

Flat suction cup (round)

SUF 25 HT1-60 G1/8-IG



Art.-Nr.: 10.01.01.14152




Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	25.00
Vacuum connection	G 1/8"-F

SUF 25 HT1-60 G1/8-IG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data

Height H	25.20 mm
Nominal diameter dn	4.10 mm
Thread G1	G 1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	2.5 mm
Diameter Ds	25.0 mm
Diameter Dmax(S)	28.2 mm

Design data SUF 25 HT1-60 G1/8-IG



WWW.SCHMALZ.COM/10.01.01.14152

1

Flat suction cup (round)

SUF 25 HT1-60 G1/8-IG



Art.-Nr.: 10.01.01.14152



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	25.0 mm
Pull-off force	23.00 N
Suction force (-600mbar)	23.00 N
Weight	10.50 g
Volume	0.900 cm ³
Size	25.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.14152

Typ		Item number
Schmalz-Connector	SC 040 G1/8-IG	10.01.06.02482
Flat suction cup (round)	SUF 25 HT1-60 SC040	10.01.01.13992



WWW.SCHMALZ.COM/10.01.01.14152