

Düz vantuz (yuvarlak)

SUF 10 NBR-55 M5-IG



Art.-Nr.: 10.01.01.14156




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	10.00
Vakum bağlantısı	M5-F

SUF 10 NBR-55 M5-IG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC



Tasarım verileri

Attribute	Value
Yükseklik H	18.40 mm
Nominal çap dn	3.10 mm
Dış G1	M5-F
Dış uzunluğu LG1	5.5 mm
Anahtar boyutu SW1	8.0 mm
Yay stroku Z	1.0 mm
Çap Ds	10.0 mm
Çap Dmax(S)	11.2 mm

Tasarım verileri SUF 10 NBR-55 M5-IG



WWW.SCHMALZ.COM/10.01.01.14156

Art.-Nr.: 10.01.01.14156

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	2.0 mm
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Çekme kuvveti	4.00 N
Emme kuvveti (-600mbar)	4.00 N
Ağırlık	1.8 g
Cilt	0.070 cm ³
Boyut	10.00
Körük Sayısı	0.0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14156

**Yedek parçalar için sipariş verileri 10.01.01.14156**

Typ	Ürün numarası
Schmalz-Konnektör	SC 030 M5-IG
Düz vantuz (yuvarlak)	SUF 10 NBR-55 SC030

