


Düz vantuz (yuvarlak)

SUF 15 NBR-55 M5-IG



Art.-Nr.: 10.01.01.14158




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	15.00
Vakum bağlantısı	M5-F

SUF 15 NBR-55 M5-IG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC



Tasarım verileri

Attribute	Value
Yükseklik H	19.00 mm
Nominal çap dn	3.10 mm
Diş G1	M5-F
Diş uzunluğu LG1	5.5 mm
Anahtar boyutu SW1	8.0 mm
Yay stroku Z	1.5 mm
Çap Ds	15.0 mm
Çap Dmax(S)	16.8 mm

Tasarım verileri SUF 15 NBR-55 M5-IG



WWW.SCHMALZ.COM/10.01.01.14158

Art.-Nr.: 10.01.01.14158

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Çekme kuvveti	9.00 N
Emme kuvveti (-600mbar)	9.00 N
Ağırlık	2.1 g
Cilt	0.220 cm ³
Boyut	15.00
Körük Sayısı	0.0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14158

**Yedek parçalar için sipariş verileri 10.01.01.14158**

Typ	Ürün numarası
Schmalz-Konnektör	SC 030 M5-IG
Düz vantuz (yuvarlak)	SUF 15 NBR-55 SC030

