

Flat suction cup (round)

SUF 15 SI-55 M5-AG



Art.-Nr.: 10.01.01.14167




Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	15.00
Vacuum connection	M5-M
Material characteristics	FDA-compatible

SUF 15 SI-55 M5-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data

Height H	13.90 mm
Nominal diameter dn	1.80 mm
Thread G1	M5-M
Thread length LG1	4.7 mm
Key width SW1	8.0 mm
Spring stroke Z	1.5 mm
Diameter Ds	15.0 mm
Diameter Dmax(S)	16.8 mm

Design data SUF 15 SI-55 M5-AG



WWW.SCHMALZ.COM/10.01.01.14167

1

Flat suction cup (round)

SUF 15 SI-55 M5-AG



Art.-Nr.: 10.01.01.14167



Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	9.00 N
Weight	1.90 g
Volume	0.220 cm ³
Size	15.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.14167

Typ		Item number
Schmalz-Connector	SC 030 M5-AG	10.01.06.02802
Flat suction cup (round)	SUF 15 SI-55 SC030	10.01.01.13967



WWW.SCHMALZ.COM/10.01.01.14167