

Flat suction cup (round)

SUF 10 SI-55 M5-IG




Art.-Nr.: 10.01.01.14168



SUF 10 SI-55 M5-IG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data SUF 10 SI-55 M5-IG

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	10.00
Vacuum connection	M5-F
Material characteristics	FDA-compatible

Design data

Attribute	Value
Height H	18.40 mm
Nominal diameter dn	3.10 mm
Thread G1	M5-F
Thread length LG1	5.5 mm
Key width SW1	8.0 mm
Spring stroke Z	1.0 mm
Diameter Ds	10.0 mm
Diameter Dmax(S)	11.2 mm



WWW.SCHMALZ.COM/10.01.01.14168

Art.-Nr.: 10.01.01.14168

**Technical data**

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	12.5 mm
Pull-off force	4.00 N
Suction force (-600mbar)	4.00 N
Weight	1.8 g
Volume	0.070 cm ³
Size	10.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14168

**Ordering Data Spare Parts 10.01.01.14168**

Typ		Item number
Schmalz-Connector	SC 030 M5-IG	10.01.06.03440
Flat suction cup (round)	SUF 10 SI-55 SC030	10.01.01.13965

