

Düz vantuz (yuvarlak)

SUF 10 SI-CO-55 M5-IG



Art.-Nr.: 10.01.01.14174



SUF 10 SI-CO-55 M5-IG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.


Mevcut yedek parçalar: vantuz SUF, konektör SC

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	10,00
Vakum bağlantısı	M5-F

Tasarım verileri

Attribute	Value
Yükseklik H	18,40 mm
Nominal çap dn	3,10 mm
Dış G1	M5-F
Dış uzunluğu LG1	5,5 mm
Anahtar boyutu SW1	8,0 mm
Yay stroku Z	1,0 mm
Çap Ds	10,0 mm
Çap Dmax(S)	11,2 mm



Tasarım verileri SUF 10 SI-CO-55 M5-IG



WWW.SCHMALZ.COM/10.01.01.14174

Art.-Nr.: 10.01.01.14174

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon Si iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Hortum çapı (tavsiye edilen) d	2,0 mm
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Çekme kuvveti	4,00 N
Emme kuvveti (-600mbar)	4,00 N
Ağırlık	1,80 g
Cilt	0,070 cm ³
Boyut	10,00
Körük Sayısı	0,0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14174

**Sipariş Verisi Yedek Parça 10.01.01.14174**

Typ	Ürün numarası
Schmalz-Konnektör	SC 030 M5-IG
Düz vantuz (yuvarlak)	SUF 10 SI-CO-55 SC030

