

Flat suction cup (round)

SUF 12 HT1-60 M5-AG



Art.-Nr.: 10.01.01.14178



SUF 12 HT1-60 M5-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.


Available spare parts: suction cup SUF, connector SC

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	12.00
Vacuum connection	M5-M

Design data

Attribute	Value
Height H	13.60 mm
Nominal diameter dn	1.80 mm
Thread G1	M5-M
Thread length LG1	4.7 mm
Key width SW1	8.0 mm
Spring stroke Z	1.2 mm
Diameter Ds	12.0 mm
Diameter Dmax(S)	13.2 mm



Design data SUF 12 HT1-60 M5-AG



WWW.SCHMALZ.COM/10.01.01.14178

Art.-Nr.: 10.01.01.14178

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	12.5 mm
Pull-off force	5.00 N
Suction force (-600mbar)	5.00 N
Weight	1.7 g
Volume	0.120 cm ³
Size	12.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14178

**Ordering Data Spare Parts 10.01.01.14178**

Typ		Item number
Schmalz-Connector	SC 030 M5-AG	10.01.06.02802
Flat suction cup (round)	SUF 12 HT1-60 SC030	10.01.01.13988

