


Düz vantuz (yuvarlak)

SUF 1.5 NBR-55 M3-AG



Art.-Nr.: 10.01.01.14198




SUF 1.5 NBR-55 M3-AG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	1.50
Vakum bağlantısı	M3-M



Tasarım verileri

Attribute	Value
Yükseklik H	4.60 mm
Nominal çap dn	1.00 mm
Dış G1	M3-M
Dış uzunluğu LG1	3.0 mm
Anahtar boyutu SW1	5.0 mm
Yay stroku Z	0.1 mm
Çap Ds	1.5 mm
Çap Dmax(S)	1.7 mm

Tasarım verileri SUF 1.5 NBR-55 M3-AG



WWW.SCHMALZ.COM/10.01.01.14198

Art.-Nr.: 10.01.01.14198

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	2.0 mm
İş parçası yarıçapı dak (dışbükey)	2.0 mm
Çekme kuvveti	0.08 N
Emme kuvveti (-600mbar)	0.08 N
Ağırlık	0.2 g
Cilt	0.001 cm ³
Boyut	1.50
Körük Sayısı	0.0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14198

**Yedek parçalar için sipariş verileri 10.01.01.14198**

Typ	Ürün numarası
Schmalz-Konnektör	SC 010 M3-AG
Düz vantuz (yuvarlak)	SUF 1.5 NBR-55 SC010

