

Düz vantuz (yuvarlak)

## SUF 2 SI-55 M3-AG



Art.-Nr.: 10.01.01.14204




### Teknik veriler

|                            |              |
|----------------------------|--------------|
| Vantuz malzemesi           | Silikon SI   |
| Malzeme sertliği [Shore A] | 55,0 Shore A |
| Boyut                      | 2,00         |
| Vakum bağlantısı           | M3-M         |
| Malzeme özellikleri        | FDA uyumlu   |

SUF 2 SI-55 M3-AG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC



### Tasarım verileri

|                    |         |
|--------------------|---------|
| Yükseklik H        | 5,50 mm |
| Nominal çap dn     | 1,00 mm |
| Diş G1             | M3-M    |
| Diş uzunluğu LG1   | 3,0 mm  |
| Anahtar boyutu SW1 | 5,0 mm  |
| Yay stroku Z       | 0,2 mm  |
| Çap Ds             | 2,0 mm  |
| Çap Dmax(S)        | 2,4 mm  |

Tasarım verileri SUF 2 SI-55 M3-AG



[WWW.SCHMALZ.COM/10.01.01.14204](http://WWW.SCHMALZ.COM/10.01.01.14204)

1

Düz vantuz (yuvarlak)

## SUF 2 SI-55 M3-AG



Art.-Nr.: 10.01.01.14204



### Teknik veriler

|                                    |                       |
|------------------------------------|-----------------------|
| Vantuz malzemesi                   | Silikon SI            |
| Malzeme sertliği [Shore A]         | 55,0 Shore A          |
| Hortum çapı (tavsiye edilen) d     | 2,0 mm                |
| İş parçası yarıçapı dak (dışbükey) | 2,0 mm                |
| Çekme kuvveti                      | 0,15 N                |
| Emme kuvveti (-600mbar)            | 0,15 N                |
| Ağırlık                            | 0,20 g                |
| Cilt                               | 0,002 cm <sup>3</sup> |
| Boyut                              | 2,00                  |
| Körük Sayısı                       | 0,0                   |
| Ürün ailesi                        | SUF                   |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Sipariş Verisi Yedek Parça 10.01.01.14204

| Typ                   |                   | Ürün numarası  |
|-----------------------|-------------------|----------------|
| Schmalz-Konnektör     | SC 010 M3-AG      | 10.01.06.04249 |
| Düz vantuz (yuvarlak) | SUF 2 SI-55 SC010 | 10.01.01.13960 |



[WWW.SCHMALZ.COM/10.01.01.14204](http://WWW.SCHMALZ.COM/10.01.01.14204)