


Flat suction cup (round)

SUF 1 HT1-60 M3-AG


Art.-Nr.: 10.01.01.14206



SUF 1 HT1-60 M3-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data SUF 1 HT1-60 M3-AG

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	1.00
Vacuum connection	M3-M

Design data

Attribute	Value
Height H	4.60 mm
Nominal diameter dn	1.00 mm
Thread G1	M3-M
Thread length LG1	3.0 mm
Key width SW1	5.0 mm
Spring stroke Z	0.1 mm
Diameter Ds	1.0 mm
Diameter Dmax(S)	1.1 mm



WWW.SCHMALZ.COM/10.01.01.14206

Art.-Nr.: 10.01.01.14206

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	2.0 mm
Pull-off force	0.03 N
Suction force (-600mbar)	0.03 N
Weight	0.2 g
Volume	0.000 cm ³
Size	1.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14206

**Ordering Data Spare Parts 10.01.01.14206**

Typ		Item number
Schmalz-Connector	SC 010 M3-AG	10.01.06.04249
Flat suction cup (round)	SUF 1 HT1-60 SC010	10.01.01.13980

