

Flat suction cup (round)

SUF 8 HT1-60 M5-AG



Art.-Nr.: 10.01.01.14232




Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	8.00
Vacuum connection	M5-M

SUF 8 HT1-60 M5-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data

Height H	10.50 mm
Nominal diameter dn	1.80 mm
Thread G1	M5-M
Thread length LG1	4.7 mm
Key width SW1	8.0 mm
Spring stroke Z	0.8 mm
Diameter Ds	8.0 mm
Diameter Dmax(S)	8.4 mm

Design data SUF 8 HT1-60 M5-AG



WWW.SCHMALZ.COM/10.01.01.14232

1

Flat suction cup (round)

SUF 8 HT1-60 M5-AG



Art.-Nr.: 10.01.01.14232



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	8.0 mm
Pull-off force	2.40 N
Suction force (-600mbar)	2.40 N
Weight	1.10 g
Volume	0.044 cm ³
Size	8.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.14232

Typ		Item number
Schmalz-Connector	SC 020 M5-AG	10.01.06.04273
Flat suction cup (round)	SUF 8 HT1-60 SC020	10.01.01.13986



WWW.SCHMALZ.COM/10.01.01.14232