

Flat suction cup (round)

## SUF 8 NBR-ESD-55 M5-IG



Art.-Nr.: 10.01.01.14241




### Technical data

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	8.00
Vacuum connection	M5-F

SUF 8 NBR-ESD-55 M5-IG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



### Design data

Height H	14.20 mm
Nominal diameter dn	1.80 mm
Thread G1	M5-F
Thread length LG1	5.5 mm
Key width SW1	8.0 mm
Spring stroke Z	0.8 mm
Diameter Ds	8.0 mm
Diameter Dmax(S)	8.4 mm

Design data SUF 8 NBR-ESD-55 M5-IG



[WWW.SCHMALZ.COM/10.01.01.14241](http://WWW.SCHMALZ.COM/10.01.01.14241)

1

Flat suction cup (round)

## SUF 8 NBR-ESD-55 M5-IG



Art.-Nr.: 10.01.01.14241



### Technical data

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	8.0 mm
Pull-off force	2.40 N
Suction force (-600mbar)	2.40 N
Weight	1.20 g
Volume	0.044 cm <sup>3</sup>
Size	8.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Ordering Data Spare Parts 10.01.01.14241

Typ		Item number
Schmalz-Connector	SC 020 M5-IG	10.01.06.04306
Flat suction cup (round)	SUF 8 NBR-ESD-55 SC020	10.01.01.14026



[WWW.SCHMALZ.COM/10.01.01.14241](http://WWW.SCHMALZ.COM/10.01.01.14241)