


Düz vantuz (yuvarlak)

SFF 30 SI-55 G1/4-IG



Art.-Nr.: 10.01.01.14257




Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	30.00
Malzeme özellikleri	FDA uyumlu

SFF 30 SI-55 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	30.80 mm
Nominal çap dn	4.00 mm
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	2.0 mm
Çap Ds	30.0 mm
Çap Dmax(S)	31.5 mm
Diş G1	G1/4-IG

Tasarım verileri SFF 30 SI-55 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.14257

Art.-Nr.: 10.01.01.14257

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Çekme kuvveti	25.10 N
Emme kuvveti (-600mbar)	25.10 N
Ağırlık	10.3 g
Cilt	1.700 cm ³
Boyut	30.00
Körük Sayısı	0.0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14257

**Yedek parçalar için sipariş verileri 10.01.01.14257**

Typ		Ürün numarası
Düz vantuz (yuvarlak)	SFF 30 SI-55 SC040	10.01.01.13749
Schmalz-Konnektör	SC 040 G1/4-IG	10.01.06.02918

