

Düz vantuz (yuvarlak)

SFF 20 EPDM-45 G1/8-IG



Art.-Nr.: 10.01.01.14265




Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	20.00

SFF 20 EPDM-45 G1/8-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	26.80 mm
Nominal çap dn	4.00 mm
Diş uzunluğu LG1	8.0 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	1.3 mm
Çap Ds	20.0 mm
Çap Dmax(S)	21.0 mm
Diş G1	G1/8-IG

Tasarım verileri SFF 20 EPDM-45 G1/8-IG



WWW.SCHMALZ.COM/10.01.01.14265

Art.-Nr.: 10.01.01.14265

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Çekme kuvveti	11.80 N
Emme kuvveti (-600mbar)	11.60 N
Ağırlık	6.7 g
Cilt	0.800 cm ³
Boyut	20.00
Körük Sayısı	0.0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14265

**Yedek parçalar için sipariş verileri 10.01.01.14265**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 20 EPDM-45 SC040 10.01.01.14046
Schmalz-Konnektör	SC 040 G1/8-IG 10.01.06.02482

