


Düz vantuz (yuvarlak)

SFF 25 EPDM-45 G1/8-IG



Art.-Nr.: 10.01.01.14267




Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	25,00

SFF 25 EPDM-45 G1/8-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	27,20 mm
Nominal çap dn	4,00 mm
Diş uzunluğu LG1	8,0 mm
Anahtar boyutu SW1	14,0 mm
Yay stroku Z	1,7 mm
Çap Ds	25,0 mm
Çap Dmax(S)	26,5 mm
Diş G1	G1/8-IG

Tasarım verileri SFF 25 EPDM-45 G1/8-IG



WWW.SCHMALZ.COM/10.01.01.14267

Art.-Nr.: 10.01.01.14267

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Çekme kuvveti	17,90 N
Emme kuvveti (-600mbar)	17,90 N
Ağırlık	7,1 g
Cilt	1,200 cm ³
Boyut	25,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14267

**Sipariş Verisi Yedek Parça 10.01.01.14267**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 25 EPDM-45 SC040
Schmalz-Konnektör	SC 040 G1/8-IG

