

Düz vantuz (yuvarlak)

SFF 30 EPDM-45 G1/4-IG



Art.-Nr.: 10.01.01.14269




Teknik veriler

Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	30,00

SFF 30 EPDM-45 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Yükseklik H	30,80 mm
Nominal çap dn	4,00 mm
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	2,0 mm
Çap Ds	30,0 mm
Çap Dmax(S)	31,5 mm
Diş G1	G1/4-IG

Tasarım verileri SFF 30 EPDM-45 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.14269

1

Düz vantuz (yuvarlak)

SFF 30 EPDM-45 G1/4-IG



Art.-Nr.: 10.01.01.14269



Teknik veriler

Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Çekme kuvveti	25,10 N
Emme kuvveti (-600mbar)	25,10 N
Ağırlık	10,30 g
Cilt	1,700 cm ³
Boyut	30,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Yedek Parça 10.01.01.14269

Typ		Ürün numarası
Düz vantuz (yuvarlak)	SFF 30 EPDM-45 SC040	10.01.01.14048
Schmalz-Konnektör	SC 040 G1/4-IG	10.01.06.02918



WWW.SCHMALZ.COM/10.01.01.14269