


Düz vantuz (yuvarlak)

SFF 40 EPDM-45 G1/4-IG



Art.-Nr.: 10.01.01.14271




Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	40.00

SFF 40 EPDM-45 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	36.20 mm
Nominal çap dn	4.00 mm
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	2.7 mm
Çap Ds	40.0 mm
Çap Dmax(S)	42.0 mm
Diş G1	G1/4-IG

Tasarım verileri SFF 40 EPDM-45 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.14271

Art.-Nr.: 10.01.01.14271

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Çekme kuvveti	47.40 N
Emme kuvveti (-600mbar)	47.40 N
Ağırlık	17.3 g
Cilt	4.300 cm ³
Boyut	40.00
Körük Sayısı	0.0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14271

**Yedek parçalar için sipariş verileri 10.01.01.14271**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 40 EPDM-45 SC050 10.01.01.14049
Schmalz-Konnektör	SC 050 G1/4-IG SW410 10.01.06.04348

