

Flat suction pad (round)

## SFF 20 HT1-60 G1/8-IG



Art.-Nr.: 10.01.01.14277




### Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	20.00

SFF 20 HT1-60 G1/8-IG

The suction cup SFF / SFB1 (elastomer part + connection nipple) is supplied assembled.

Available spare parts: suction cup SFF / SFB1, connection nipple SC



### Design data

Height H	26.80 mm
Nominal diameter dn	4.00 mm
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	1.3 mm
Diameter Ds	20.0 mm
Diameter Dmax(S)	21.0 mm
Thread G1	G1/8-IG

Design data SFF 20 HT1-60 G1/8-IG



[WWW.SCHMALZ.COM/10.01.01.14277](http://WWW.SCHMALZ.COM/10.01.01.14277)

1

Flat suction pad (round)

## SFF 20 HT1-60 G1/8-IG



Art.-Nr.: 10.01.01.14277



### Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Pull-off force	11.80 N
Suction force (-600mbar)	11.60 N
Weight	6.70 g
Volume	0.800 cm <sup>3</sup>
Size	20.00
Number of folds	0.0
Product family	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Ordering Data Spare Parts 10.01.01.14277

Typ		Item number
Flat suction cup (round)	SFF 20 HT1-60 SC040	10.01.01.14052
Schmalz-Connector	SC 040 G1/8-IG	10.01.06.02482



[WWW.SCHMALZ.COM/10.01.01.14277](http://WWW.SCHMALZ.COM/10.01.01.14277)