


Flat suction cup (round)

SUF 3 HT1-60 SC010


Art.-Nr.: 10.01.01.14288



SUF 3 HT1-60 SC010

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	3.00



Design data SUF 3 HT1-60 SC010

Design data

Attribute	Value
Height H2	2.00 mm
Height H	3.50 mm
Head diameter Dk	4.2 mm
Internal diameter d	1.40 mm
Spring stroke Z	0.3 mm
Diameter Ds	3.0 mm
Diameter Dmax(S)	3.7 mm



WWW.SCHMALZ.COM/10.01.01.14288

Flat suction cup (round)

SUF 3 HT1-60 SC010



Art.-Nr.: 10.01.01.14288



Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Workpiece radius min. (convex)	8.0 mm
Pull-off force	0.30 N
Suction force (-600mbar)	0.30 N
Weight	0.0 g
Volume	0.003 cm ³
Size	3.00
Product family	SUF
Interface nipple family	SC010

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14288



Ordering Data Accessories 10.01.01.14288

Typ		Item number
Schmalz-Connector	SC 010 M3-AG	10.01.06.04249



WWW.SCHMALZ.COM/10.01.01.14288