

Art.-Nr.: 10.01.01.14316



SUF 125 NBR-60 G1/4-IG VRS

Technical data


Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	125.00
contains	Screw plug
Suction cup area	136 cm ²

Suction plate SUF (sealing ring + support plate) is delivered pre-assembled. The product consists of:

- Sealing ring of type DR-SUF – elastomer part, available in various diameters
- Reinforced plastic support plate with various threads

Available spare parts: sealing ring DR-SUF

Available accessories: touch valve TV, screen



Design data SUF 125 NBR-60 G1/4-IG VRS

Design data

Attribute	Value
Length L2	22.00 mm
Height H	29.00 mm
d2	98.0 mm
Thread G1	G1/4"-F
Thread length LG1	11.8 mm
Thread G2	G1/8"-F
Thread length LG2	9.5 mm
Spring stroke Z	8.0 mm
Diameter Ds	125.0 mm
Diameter Dmax(S)	132.0 mm

Art.-Nr.: 10.01.01.14316

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Workpiece radius min. (convex)	250.0 mm
Suction force (-600mbar)	730.00 N
Weight	195.0 g
Volume	96.000 cm ³
Size	125.00
Suction force d2	450.00 N
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14316

**Ordering Data Accessories 10.01.01.14316**

Typ		Item number
Sieve, round	SIEB 15x0.8 MS-A2 0.103/0.07	10.07.01.00211
Protection Covers	PC 150	10.01.01.13087
Touch Valve	TV G1/8-AG 10	10.05.10.00088

**Ordering Data Spare Parts 10.01.01.14316**

Typ		Item number
Sealing ring for SUF suction plate	DR-SUF 125 NBR-60	10.01.01.14319

