


Art.-Nr.: 10.01.01.14327



DR-SUF 160 NBR-60

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	160.00



Design data DR-SUF 160 NBR-60

Design data

Attribute	Value
Height H	29.80 mm
d2	130.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	160.0 mm
Diameter Dmax(S)	170.0 mm



Art.-Nr.: 10.01.01.14327



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Weight	137.0 g
Size	160.00

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14327

