

Flat suction cup (round)

SFF 10 NBR-ESD-55 SC030

Art.-Nr.: 10.01.01.14328




SFF 10 NBR-ESD-55 SC030

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	10.00
Number of folds	0.0

Design data

Attribute	Value
Height H2	4.20 mm
Height H	10.40 mm
Head diameter Dk	9.3 mm
Internal diameter d1	7.3 mm
Internal diameter d	5.50 mm
Spring stroke Z	0.7 mm
Diameter Ds	10.0 mm
Height H3	5.90 mm
Diameter Dmax(S)	11.0 mm



Design data SFF 10 NBR-ESD-55 SC030



WWW.SCHMALZ.COM/10.01.01.14328

Art.-Nr.: 10.01.01.14328

**Technical data**

Attribute	Value
Nipple family	SC 030
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	8.0 mm
Pull-off force	3.00 N
Suction force (-600mbar)	2.70 N
Weight	0.40 g
Volume	0.245 cm ³
Size	10.00
Number of folds	0.0
Product family	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14328

**Ordering Data Accessories 10.01.01.14328**

Typ		Item number
Schmalz-Connector	SC 030 M5-AG	10.01.06.02802

