

Düz vantuz (yuvarlak)

## PFG 25 NBR-ESD-55 N007


Art.-Nr.: 10.01.01.14343



### Teknik veriler

| Attribute                  | Value                 |
|----------------------------|-----------------------|
| Vantuz malzemesi           | Nitril kauçuk NBR-ESD |
| Malzeme sertliği [Shore A] | 55,0 Shore A          |
| Boyut                      | 25,00                 |

PFG 25 NBR-ESD-55 N007



### Tasarım verileri

| Attribute                                                                                   | Value    |
|---------------------------------------------------------------------------------------------|----------|
| Yükseklik H2                                                                                | 7,00 mm  |
| Yükseklik H                                                                                 | 14,00 mm |
| Kafa çapı Dk                                                                                | 16,2 mm  |
| İç çap d1                                                                                   | 11,0 mm  |
| İç çap d                                                                                    | 6,00 mm  |
| Yay stroku Z                                                                                | 3,0 mm   |
| Çap Ds                                                                                      | 25,0 mm  |
| Çap Dmax(S)                                                                                 | 27,5 mm  |
| Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları |          |

Tasarım verileri PFG 25 NBR-ESD-55 N007



[WWW.SCHMALZ.COM/10.01.01.14343](http://WWW.SCHMALZ.COM/10.01.01.14343)

Art.-Nr.: 10.01.01.14343

**Teknik veriler**

| Attribute                          | Value                 |
|------------------------------------|-----------------------|
| Meme ucu ailesi                    | N 007                 |
| Vantuz malzemesi                   | Nitril kauçuk NBR-ESD |
| Malzeme sertliği [Shore A]         | 55,0 Shore A          |
| İş parçası yarıçapı dak (dışbükey) | 25,0 mm               |
| Emme kuvveti (-600mbar)            | 26,50 N               |
| Ağırlık                            | 2,40 g                |
| Cilt                               | 1,483 cm <sup>3</sup> |
| Boyut                              | 25,00                 |
| Ürün ailesi                        | PFG                   |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.01.14343](http://www.schmalz.com/10.01.01.14343)

**Sipariş Verisi Aksesuarlar 10.01.01.14343**

| Typ                   | Ürün numarası             |
|-----------------------|---------------------------|
| Vantuz bağlantı nipel | SA-NIP N007 G1/8-AG DN240 |
| Vantuz bağlantı nipel | SA-NIP N007 G1/8-IG DN350 |

[WWW.SCHMALZ.COM/10.01.01.14343](http://WWW.SCHMALZ.COM/10.01.01.14343)