

Düz vantuz (yuvarlak)

SFF 15 NBR-ESD-55 M5-AG



Art.-Nr.: 10.01.01.14536




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	15,00

SFF 15 NBR-ESD-55 M5-AG

Vantuz SFF (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	17,50 mm
Nominal çap dn	1,80 mm
Dış uzunluğu LG1	4,7 mm
Anahtar boyutu SW1	10,0 mm
Yay stroku Z	1,0 mm
Çap Ds	15,0 mm
Çap Dmax(S)	16,0 mm
Dış G1	M5-AG

Tasarım verileri SFF 15 NBR-ESD-55 M5-AG



WWW.SCHMALZ.COM/10.01.01.14536

Art.-Nr.: 10.01.01.14536

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Çekme kuvveti	5,80 N
Emme kuvveti (-600mbar)	5,80 N
Ağırlık	2,10 g
Cilt	0,600 cm ³
Boyut	15,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14536

**Sipariş Verisi Yedek Parça 10.01.01.14536**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 15 NBR-ESD-55 SC040
Schmalz-Konnektör	SC 040 M5-AG

