


Düz vantuz (yuvarlak)

SFF 15 NBR-ESD-55 G1/8-IG



Art.-Nr.: 10.01.01.14538




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	15.00

SFF 15 NBR-ESD-55 G1/8-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	26.50 mm
Nominal çap dn	4.00 mm
Diş uzunluğu LG1	8.0 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	1.0 mm
Çap Ds	15.0 mm
Çap Dmax(S)	16.0 mm
Diş G1	G1/8-IG

Tasarım verileri SFF 15 NBR-ESD-55 G1/8-IG



WWW.SCHMALZ.COM/10.01.01.14538

Art.-Nr.: 10.01.01.14538

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Çekme kuvveti	5.80 N
Emme kuvveti (-600mbar)	5.80 N
Ağırlık	6.2 g
Cilt	0.600 cm ³
Boyut	15.00
Körük Sayısı	0.0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14538

**Yedek parçalar için sipariş verileri 10.01.01.14538**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 15 NBR-ESD-55 SC040
Schmalz-Konnektör	SC 040 G1/8-IG

