

Düz vantuz (yuvarlak)

SFF 10 NBR-ESD-55 M5-AG



Art.-Nr.: 10.01.01.14671




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	10,00

SFF 10 NBR-ESD-55 M5-AG

Vantuz SFF (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	15,40 mm
Nominal çap dn	1,80 mm
Diş uzunluğu LG1	4,7 mm
Anahtar boyutu SW1	8,0 mm
Yay stroku Z	0,7 mm
Çap Ds	10,0 mm
Çap Dmax(S)	11,0 mm
Diş G1	M5-AG

Tasarım verileri SFF 10 NBR-ESD-55 M5-AG



WWW.SCHMALZ.COM/10.01.01.14671

Art.-Nr.: 10.01.01.14671

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Çekme kuvveti	3,00 N
Emme kuvveti (-600mbar)	2,70 N
Ağırlık	1,60 g
Cilt	0,250 cm ³
Boyut	10,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14671

**Sipariş Verisi Yedek Parça 10.01.01.14671**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 10 NBR-ESD-55 SC030
Schmalz-Konnektör	SC 030 M5-AG

