

Düz vantuz (yuvarlak)

SFF 40 NBR-ESD-55 G1/4-IG



Art.-Nr.: 10.01.01.14679




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	40,00

SFF 40 NBR-ESD-55 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	36,20 mm
Nominal çap dn	4,00 mm
Dış uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	2,7 mm
Çap Ds	40,0 mm
Çap Dmax(S)	42,0 mm
Dış G1	G1/4-IG

Tasarım verileri SFF 40 NBR-ESD-55 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.14679

Art.-Nr.: 10.01.01.14679

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Çekme kuvveti	47,40 N
Emme kuvveti (-600mbar)	47,40 N
Ağırlık	17,30 g
Cilt	4,300 cm ³
Boyut	40,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14679

**Sipariş Verisi Yedek Parça 10.01.01.14679**

Typ	Ürün numarası
Düz vantuz (yuvarlak)	SFF 40 NBR-ESD-55 SC050
Schmalz-Konnektör	SC 050 G1/4-IG SW410

