

Flat suction cup (round)

SUF 30 HT1-60 NPT1/4-AG



Art.-Nr.: 10.01.01.15055



SUF 30 HT1-60 NPT1/4-AG


Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	30.00
Vacuum connection	NPT1/4-M

Design data



Attribute	Value
Height H	17.70 mm
Nominal diameter dn	4.10 mm
Thread G1	NPT1/4" -M
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	3.0 mm
Diameter Ds	30.0 mm
Diameter Dmax(S)	33.3 mm

Design data SUF 30 HT1-60 NPT1/4-AG



WWW.SCHMALZ.COM/10.01.01.15055

Art.-Nr.: 10.01.01.15055

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	35.0 mm
Pull-off force	34.00 N
Weight	11.20 g
Volume	1.600 cm ³
Size	30.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.15055

**Ordering Data Spare Parts 10.01.01.15055**

Typ		Item number
Schmalz-Connector	SC 040 NPT1/4-AG	10.01.06.04922
Flat suction cup (round)	SUF 30 HT1-60 SC040	10.01.01.13993

