

Flat suction cup (round)

SUF 60 NBR-55 NPT1/4-AG



Art.-Nr.: 10.01.01.15140



SUF 60 NBR-55 NPT1/4-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.


Available spare parts: suction cup SUF, connector SC

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	60.00
Vacuum connection	NPT1/4-M

Design data

Attribute	Value
Height H	22.00 mm
Nominal diameter dn	5.50 mm
Thread G1	NPT1/4"-M
Thread length LG1	16.0 mm
Key width SW1	22.0 mm
Spring stroke Z	5.5 mm
Diameter Ds	60.0 mm
Diameter Dmax(S)	66.4 mm



Design data SUF 60 NBR-55 NPT1/4-AG



WWW.SCHMALZ.COM/10.01.01.15140

Art.-Nr.: 10.01.01.15140

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	75.0 mm
Pull-off force	140.00 N
Suction force (-600mbar)	140.00 N
Weight	38.60 g
Volume	12.700 cm ³
Size	60.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.15140

**Ordering Data Spare Parts 10.01.01.15140**

Typ		Item number
Reduction nipple with hexagon	RED-NIP NPT1/4-AG AL	10.01.01.15181
Flat suction cup (round)	SUF 60 NBR-55 M10x1.25-IG N009	10.01.01.13953

