


Плоская присоска (круглая)

SFF 60 EPDM-45 SC080

Art.-Nr.: 10.01.01.15210



SFF 60 EPDM-45 SC080

Технические данные

Attribute	Value
Материал присоски	EPDM
Твердость материала [Shore A]	45.0 Shore A
размер	60.00
Количество складок	0.0

Конструктивные данные

Attribute	Value
Высота H2	13.00 mm
Высота H	29.00 mm
Диаметр головки Dk	30.0 mm
Внутренний диаметр d1	22.0 mm
Внутренний диаметр d	16.00 mm
Ход пружины Z	4.0 mm
Диаметр Ds	60.0 mm
Высота H3	15.90 mm
Диаметр Dmax(S)	64.0 mm

Конструктивные данные SFF 60 EPDM-45 SC080



WWW.SCHMALZ.COM/10.01.01.15210

Art.-Nr.: 10.01.01.15210



Технические данные

Attribute	Value
Семейство ниппелей	SC 080
Материал присоски	EPDM
Твердость материала [Shore A]	45.0 Shore A
Радиус заготовки мин. (выпуклый)	67.5 mm
Сила отрыва	90.00 N
Всасывающая сила (-600 мбар)	90.00 N
Вес	20.3 g
Объем	9.910 cm ³
размер	60.00
Количество складок	0.0
Семейство продуктов	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.15210

