


Düz vantuz (yuvarlak)

SFF 60 EPDM-45 SC080



Art.-Nr.: 10.01.01.15210



SFF 60 EPDM-45 SC080

Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	60.00
Körük Sayısı	0.0

Tasarım verileri

Attribute	Value
Yükseklik H2	13.00 mm
Yükseklik H	29.00 mm
Kafa çapı Dk	30.0 mm
İç çap d1	22.0 mm
İç çap d	16.00 mm
Yay stroku Z	4.0 mm
Çap Ds	60.0 mm
Yükseklik H3	15.90 mm
Çap Dmax(S)	64.0 mm

Tasarım verileri SFF 60 EPDM-45 SC080



WWW.SCHMALZ.COM/10.01.01.15210

Art.-Nr.: 10.01.01.15210



Teknik veriler

Attribute	Value
Meme ucu ailesi	SC 080
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
İş parçası yarıçapı dak (dışbükey)	67.5 mm
Çekme kuvveti	90.00 N
Emme kuvveti (-600mbar)	90.00 N
Ağırlık	20.3 g
Cilt	9.910 cm ³
Boyut	60.00
Körük Sayısı	0.0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.15210

