

Flat suction pad (round)

SFF 60 HT1-60 G1/4-IG



Art.-Nr.: 10.01.01.15578




Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	60.00

SFF 60 HT1-60 G1/4-IG

The suction cup SFF / SFB1 (elastomer part + connection nipple) is supplied assembled.

Available spare parts: suction cup SFF / SFB1, connection nipple SC



Design data

Height H	46.50 mm
Nominal diameter dn	4.00 mm
Thread length LG1	12.0 mm
Key width SW1	22.0 mm
Spring stroke Z	4.0 mm
Diameter Ds	60.0 mm
Diameter Dmax(S)	64.0 mm
Thread G1	G1/4-IG

Design data SFF 60 HT1-60 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.15578

Flat suction pad (round)

SFF 60 HT1-60 G1/4-IG



Art.-Nr.: 10.01.01.15578



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Pull-off force	90.00 N
Suction force (-600mbar)	90.00 N
Size	60.00
Number of folds	0.0
Product family	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.15578

Typ		Item number
Flat suction cup (round)	SFF 60 HT1-60 SC080	10.01.01.15243
Schmalz-Connector	SC 080 G1/4-IG	10.01.06.03271



WWW.SCHMALZ.COM/10.01.01.15578