




FSTE G1/4-AG 50

Yaylı piston FSTE bağlanmaya hazır bir ürün olarak teslim edilir.



Tasarım verileri FSTE G1/4-AG 50

Teknik veriler

Yay stroku Z	50,0 mm
Vantuz bağlantısı	G1/4"-M
Vakum bağlantısı	G1/8"-F
Tightening torque (max)	40,0 Nm

Tasarım verileri

Yükseklik H2	70,00 mm
Yükseklik H	115,50 mm
Diş G1	G1/8"-F
Diş uzunluğu LG1	13,0 mm
Diş G2	G1/4"-M
Diş uzunluğu LG2	8,5 mm
Diş uzunluğu LG3	40,0 mm
Anahtar boyutu SW1	24,0 mm
Anahtar boyutu SW2	17,0 mm
Yay stroku Z	50,0 mm
Anahtar boyutu SW3	17,0 mm
Diş G3	M20x1.5-M

Art.-Nr.: 10.01.02.00568

**Teknik veriler**

Yay kuvveti merkezi	12,70 N
Yay oranı	0,452 N/mm
Yay ön gerilimi	1,40 N
Yatay yük	466,0 N
Dikey yük	2.400,0 N
Ağırlık	175,00 g
Çalışma sıcaklığı	0 ... 80 °C
Ürün ailesi	FSTE
Tightening torque (max)	40,0 Nm

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Sipariş Verisi Aksesuarlar 10.01.02.00568**

Typ	Ürün numarası
Flexolink	FLK G1/4-IG G1/4-AG
Bilyalı mafsal	KGL G1/4-IG G1/4-AG
Bilyalı mafsal	KGL G1/4-IG M10x1.25-AG
Flexolink	FLK G1/4-IG M10x1.25-AG
Çapraz kiriş bağlantısı	HTR-STA 55 1N D20 WI
Üniversal tutucu	HTR-UNI 2N FSTE-HDB
Hortum manşonu	ST G1/8-AG 4 MS-ROH
Hortum manşonu	ST G1/8-AG 6 MS-V
Hortum manşonu	ST G1/8-AG 9 MS-V
Otomatik rakor, düz	STV-GE G1/8-AG 4
Otomatik rakor, düz	STV-GE G1/8-AG 6
Otomatik rakor, düz	STV-GE G1/8-AG 8
Tapa rakoru, dirsek	STV-W G1/8-AG 4
Tapa rakoru, dirsek	STV-W G1/8-AG 6
Tapa rakoru, dirsek	STV-W G1/8-AG 8
Otomatik rakor, düz	STV-GE G1/8-AG 6 HT
Tapa rakoru, dirsek	STV-W G1/8-AG 6
Tapa rakoru, dirsek	STV-W G1/8-AG 6 HT
Tapa rakoru, dirsek	STV-WF G1/8-AG 4
Tapa rakoru, dirsek	STV-WF G1/8-AG 6
Tapa rakoru, dirsek	STV-WF G1/8-AG 8
Tapa rakoru, dirsek	STV-WF G1/8-AG 10
Fiş birleşimi, T	STV-T G1/8-AG 4
Fiş birleşimi, T	STV-T G1/8-AG 6
Fiş birleşimi, T	STV-T G1/8-AG 8



Yaylı piston

FSTE G1/4-AG 50



Art.-Nr.: 10.01.02.00568



Sipariş Verisi Yedek Parça 10.01.02.00568

Typ	Ürün numarası
Basınç yayı	DRUCK-FED 1.1x15.7 68.08 0.453
	20.08.02.00231



WWW.SCHMALZ.COM/10.01.02.00568