




FSTA G1/4-AG 25

Yaylı bağlantı FSTA bağlanmaya hazır bir ürün olarak teslim edilir.



Tasarım verileri FSTA G1/4-AG 25

Teknik veriler

Attribute	Value
Yay stroku Z	25.0 mm
Vantuz bağlantısı	G1/4"-M
Vakum bağlantısı	G1/8"-F

Tasarım verileri

Attribute	Value
Yükseklik H2	37.00 mm
Yükseklik H	114.50 mm
Diş G1	G1/8"-F
Diş uzunluğu LG1	12.0 mm
Diş G2	G1/4"-M
Diş uzunluğu LG2	8.5 mm
Diş G3	M20x1.5-AG
Diş uzunluğu LG3	40.0 mm
Anahtar boyutu SW1	24.0 mm
Anahtar boyutu SW2	17.0 mm

Art.-Nr.: 10.01.02.00572

**Teknik veriler**

Attribute	Value
Yay kuvveti merkezi	17.80 N
Yay oranı	0.711 N/mm
Yay ön gerilimi	8.95 N
Yatay yük	800.0 N
Dikey yük	2400.0 N
Ağırlık	185.0 g
Çalışma sıcaklığı	0 ... 80 °C

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.02.00572

WWW.SCHMALZ.COM/10.01.02.00572

Art.-Nr.: 10.01.02.00572



Veri aksesuarları sipariş edin 10.01.02.00572

Typ		Ürün numarası
Flexolink	FLK G1/4-IG G1/4-AG	10.01.03.00178
Bilyalı mafsal	KGL G1/4-IG G1/4-AG	10.01.03.00110
Bilyalı mafsal	KGL G1/4-IG M10x1.25-AG	10.01.03.00137
Flexolink	FLK G1/4-IG M10x1.25-AG	10.01.03.00206
Çapraz giriş bağlantısı	HTR-STA 55 1N D20 WI	10.08.03.00086
Üniversal tutucu	HTR-UNI 2N FSTE-HDB	10.01.03.00332
Hortum manşonu	ST G1/8-AG 4 M5-ROH	10.08.03.00153
Hortum manşonu	ST G1/8-AG 6 M5-V	10.08.03.00154
Hortum manşonu	ST G1/8-AG 9 M5-V	10.08.03.00155
Otomatik rakor, düz	STV-GE G1/8-AG 4	10.08.02.00202
Otomatik rakor, düz	STV-GE G1/8-AG 6	10.08.02.00204
Otomatik rakor, düz	STV-GE G1/8-AG 6 HT	10.08.02.00389
Otomatik rakor, düz	STV-GE G1/8-AG 8	10.08.02.00206
Fiş birleşimi, T	STV-T G1/8-AG 4	10.09.02.00039
Fiş birleşimi, T	STV-T G1/8-AG 6	10.09.02.00040
Fiş birleşimi, T	STV-T G1/8-AG 8	10.09.02.00041
Tapa rakoru, dirsek	STV-W G1/8-AG 4	10.08.02.00156
Tapa rakoru, dirsek	STV-W G1/8-AG 6	10.08.02.00288
Tapa rakoru, dirsek	STV-W G1/8-AG 6	10.08.02.00158
Tapa rakoru, dirsek	STV-W G1/8-AG 6 HT	10.08.02.00391
Tapa rakoru, dirsek	STV-W G1/8-AG 8	10.08.02.00160
Tapa rakoru, dirsek	STV-WF G1/8-AG 10	10.08.02.00257
Tapa rakoru, dirsek	STV-WF G1/8-AG 4	10.08.02.00166
Tapa rakoru, dirsek	STV-WF G1/8-AG 6	10.08.02.00168
Tapa rakoru, dirsek	STV-WF G1/8-AG 8	10.08.02.00170

