




FSTA G1/2-AG 25

Yaylı bağlantı FSTA bağlanmaya hazır bir ürün olarak teslim edilir.



Tasarım verileri FSTA G1/2-AG 25

**Teknik veriler**

| Attribute               | Value   |
|-------------------------|---------|
| Yay stroku Z            | 25.0 mm |
| Vantuz bağlantısı       | G1/2"-M |
| Vakum bağlantısı        | G3/8"-F |
| Tightening torque (max) | 50.0 Nm |

**Tasarım verileri**

| Attribute          | Value     |
|--------------------|-----------|
| Yükseklik H2       | 42.50 mm  |
| Yükseklik H        | 146.50 mm |
| Diş G1             | G3/8"-F   |
| Diş uzunluğu LG1   | 12.0 mm   |
| Diş G2             | G1/2"-M   |
| Diş uzunluğu LG2   | 10.5 mm   |
| Diş uzunluğu LG3   | 55.0 mm   |
| Anahtar boyutu SW1 | 36.0 mm   |
| Anahtar boyutu SW2 | 24.0 mm   |
| Yay stroku Z       | 25.0 mm   |

Art.-Nr.: 10.01.02.00577

**Teknik veriler**

| Attribute               | Value       |
|-------------------------|-------------|
| Yay kuvveti merkezi     | 73.50 N     |
| Yay oranı               | 3.828 N/mm  |
| Yay ön gerilimi         | 25.65 N     |
| Yatay yük               | 1870.0 N    |
| Dikey yük               | 4900.0 N    |
| Ağırlık                 | 493.0 g     |
| Çalışma sıcaklığı       | 0 ... 80 °C |
| Ürün ailesi             | FSTA        |
| Tightening torque (max) | 50.0 Nm     |

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.02.00577](http://www.schmalz.com/10.01.02.00577)

**Veri aksesuarları sipariş edin 10.01.02.00577**

| Typ                     |                       | Ürün numarası  |
|-------------------------|-----------------------|----------------|
| Flexolink               | FLK G1/2-IG G1/2-AG   | 10.01.03.00175 |
| Flexolink               | FLK G1/2-IG G1/2-AG V | 10.01.03.00207 |
| Çapraz giriş bağlantısı | HTR-STA 62 1N D30 WI  | 10.08.03.00148 |
| Çapraz giriş bağlantısı | HTR-ST5 40x40 D30 WI  | 10.08.03.00090 |
| Çapraz giriş bağlantısı | HTR-ST5 50x50 D30 WI  | 10.08.03.00091 |
| Çapraz giriş bağlantısı | HTR-ST5 60x60 D30 WI  | 10.08.03.00092 |
| Bilyalı mafsal          | KGL G1/2-IG G1/2-AG   | 10.01.03.00111 |
| Hortum manşonu          | ST G3/8-AG 13 MS-V    | 10.08.03.00160 |
| Hortum manşonu          | ST G3/8-AG 9 MS-V     | 10.08.03.00159 |
| Otomatik rakor, düz     | STV-GE G3/8-AG 10     | 10.08.02.00252 |
| Otomatik rakor, düz     | STV-GE G3/8-AG 12     | 10.08.02.00209 |
| Otomatik rakor, düz     | STV-GE G3/8-AG 14     | 10.08.02.00211 |
| Otomatik rakor, düz     | STV-GE G3/8-AG 8      | 10.08.02.00237 |
| Tapa rakoru, dirsek     | STV-W G3/8-AG 10      | 10.08.02.00255 |
| Tapa rakoru, dirsek     | STV-W G3/8-AG 12      | 10.08.02.00163 |
| Tapa rakoru, dirsek     | STV-W G3/8-AG 8       | 10.08.02.00236 |
| Tapa rakoru, dirsek     | STV-WF G3/8-AG 10     | 10.08.02.00259 |
| Tapa rakoru, dirsek     | STV-WF G3/8-AG 8      | 10.08.02.00234 |

[WWW.SCHMALZ.COM/10.01.02.00577](http://WWW.SCHMALZ.COM/10.01.02.00577)