




FSTE M3-IG 5 VG

Yaylı piston FSTE bağlanmaya hazır bir ürün olarak teslim edilir.



Tasarım verileri FSTE M3-IG 5 VG

Teknik veriler

Attribute	Value
Şekil montaj elemanları	dönme önleyici korumalı
Yay stroku Z	5.0 mm
Vantuz bağlantısı	M3-F
Vakum bağlantısı	M3-F

Tasarım verileri

Attribute	Value
Yükseklik H2	15.00 mm
Yükseklik H	33.50 mm
Diş G1	M3-F
Diş uzunluğu LG1	3.8 mm
Diş G2	M3-F
Diş uzunluğu LG2	6.0 mm
Diş uzunluğu LG3	10.0 mm
Anahtar boyutu SW1	10.0 mm
Anahtar boyutu SW2	4.5 mm
Yay stroku Z	5.0 mm

Art.-Nr.: 10.01.02.00614

**Teknik veriler**

Attribute	Value
Yay kuvveti merkezi	2.98 N
Yay oranı	0.596 N/mm
Yay ön gerilimi	1.49 N
Yatay yük	47.0 N
Dikey yük	550.0 N
Ağırlık	9.0 g
Çalışma sıcaklığı	0 ... 80 °C
Ürün ailesi	FSTE

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.02.00614

**Yedek parçalar için sipariş verileri 10.01.02.00614**

Typ	Ürün numarası
Basınç yayı	DRUCK-FED 0.4x5 10.5 0.596
	20.08.02.00093

