


Art.-Nr.: 10.01.02.00864



FSTI G1/4-AG G1/8-AG 10

Yaylı piston FSTI, bağlanmaya hazır bir ürün olarak teslim edilir.



Tasarım verileri FSTI G1/4-AG G1/8-AG 10

Teknik veriler

Attribute	Value
Yay stroku Z	10.0 mm
Vantuz bağlantısı	G1/4"-M
Vakum bağlantısı	G1/8"-M
Tightening torque (max)	40.0 Nm

Tasarım verileri

Attribute	Value
Yükseklik H2	21.00 mm
Yükseklik H	71.00 mm
Diş G1	G1/8"-M
Diş uzunluğu LG1	6.5 mm
Diş G2	G1/4"-M
Diş uzunluğu LG2	10.0 mm
Diş uzunluğu LG3	41.0 mm
Anahtar boyutu SW1	27.0 mm
Anahtar boyutu SW2	13.0 mm
Yay stroku Z	10.0 mm

Art.-Nr.: 10.01.02.00864

**Teknik veriler**

Attribute	Value
Yay kuvveti merkezi	7.57 N
Yay oranı	0.097 N/mm
Yay ön gerilimi	7.08 N
Yatay yük	700.0 N
Dikey yük	1000.0 N
Ağırlık	150.0 g
Çalışma sıcaklığı	0 ... 80 °C
Ürün ailesi	FSTI
Tightening torque (max)	40.0 Nm

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.02.00864

**Veri aksesuarları sipariş edin 10.01.02.00864**

Typ		Ürün numarası
Flexolink	FLK G1/4-IG G1/4-AG	10.01.03.00178
Flexolink	FLK G1/4-IG M10x1.25-AG	10.01.03.00206
Yaylı bağlantı tutucusu	HTR-FST A2 FSTI	10.01.03.06134
Yaylı bağlantı tutucusu	HTR-FST A3 FSTI	10.01.03.06136
Yaylı bağlantı tutucusu	HTR-FST 2N	10.01.03.06143
Üniversal tutucu	HTR-UNI 2N FSTI	10.01.03.00297
Bilyalı mafsal	KGL G1/4-IG G1/4-AG	10.01.03.00110
Bilyalı mafsal	KGL G1/4-IG M10x1.25-AG	10.01.03.00137
Otomatik rakor, düz	STVI-GE G1/8-IG 4	10.08.02.00149
Otomatik rakor, düz	STVI-GE G1/8-IG 6	10.08.02.00150
Otomatik rakor, düz	STVI-GE G1/8-IG 8	10.08.02.00151

WWW.SCHMALZ.COM/10.01.02.00864