




FSTF G1/2-AG 50

Yaylı bağlantı FSTF bağlanmaya hazır bir ürün olarak teslim edilir.

Mevcut aksesuarlar: montaj seti

Teknik veriler

Attribute	Value
Yay stroku Z	50.0 mm
Vantuz bağlantısı	G1/4"-F
Vakum bağlantısı	M20x1.5-M
alternatif vakum bağlantısı	G1/4"-F
alternatif vantuz bağlantısı	G1/2"-M



Tasarım verileri FSTF G1/2-AG 50

Tasarım verileri

Attribute	Value
Uzunluk L	60.00 mm
Genişlik B1	54.60 mm
Genişlik B	32.30 mm
Yükseklik H2	85.00 mm
Yükseklik H	168.00 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	10.0 mm
Diş G2	G1/2"-M
Diş uzunluğu LG2	12.0 mm
Diş uzunluğu LG3	10.0 mm

Art.-Nr.: 10.01.02.01012

**Teknik veriler**

Attribute	Value
Yay kuvveti merkezi	31.75 N
Yay oranı	0.567 N/mm
Yay ön gerilimi	17.60 N
Yatay yük	800.0 N
Dikey yük	2500.0 N
Ağırlık	246.0 g
Çalışma sıcaklığı	0 ... 50 °C
Ürün ailesi	FSTF
alternatif vakum bağlantısı	G1/4"-F
alternatif vantuz bağlantısı	G1/2"-M

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.02.01012

**Veri aksesuarları sipariş edin 10.01.02.01012**

Typ	Ürün numarası
Montaj seti	SET FSTF 10.01.02.01030
Montaj seti	SET FSTF COM 10.01.02.01031

WWW.SCHMALZ.COM/10.01.02.01012