


Art.-Nr.: 10.01.02.01441



FSTE-HDB G1/2-AG 80 VG-AB

Spring plunger FSTE-HDB is delivered as a ready-to-connect product.



Design data FSTE-HDB G1/2-AG 80 VG-AB

**Technical data**

Shape mounting elements	with anti-rotation guard anti-block
Spring stroke Z	80.0 mm
Suction cup connection	G 1/2"-M
Vacuum connection	G3/8"-F
Tightening torque (max)	50.0 Nm

**Design data**

Height H2	91.80 mm
Height H	216.30 mm
Thread G1	G3/8"-F
Thread length LG1	16.0 mm
Thread G2	G1/2"-M
Thread length LG2	10.5 mm
Thread length LG3	50.0 mm
Key width SW1	36.0 mm
Spanner size SW2	24.0 mm
Spring stroke Z	80.0 mm
Key width SW3	32.0 mm
Thread G3	M30x1.5-M

Recommendation: Avoid maximum plunger stroke Z during continuous operation to extend service life. Ensure that the hose guide is free from distortion.



Art.-Nr.: 10.01.02.01441

**Technical data**

Shape mounting elements	with anti-rotation guard anti-block
Spring force center	64.50 N
Spring rate	1.072 N/mm
Spring pretension	21.50 N
Horizontal load	800.0 N
Vertical load	4,900.0 N
Weight	725.00 g
Operating temperature	0 ... 80 °C
Product family	FSTE-HDB
Tightening torque (max)	50.0 Nm

Note: Spring force: Referred to 50 % of operating stroke Vertical load: Maximum static loading Horizontal load: The specification of the horizontal load refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position.

**Ordering Data Accessories 10.01.02.01441**

Typ		Item number
Universal holder	HTR-UNI 2N FSTE-HDB	10.01.03.00332
Flexolink	FLK G1/2-IG G1/2-AG	10.01.03.00175
Flexolink	FLK G1/2-IG G1/2-AG V	10.01.03.00207
Ball joint	KGL G1/2-IG G1/2-AG	10.01.03.00111
Cross-beam connection	HTR-STA 62 1N D30 WI	10.08.03.00148
Cross-beam connection	HTR-ST5 40x40 D30 WI	10.08.03.00090
Cross-beam connection	HTR-ST5 50x50 D30 WI	10.08.03.00091
Cross-beam connection	HTR-ST5 60x60 D30 WI	10.08.03.00092
Hose sleeve	ST G3/8-AG 9 MS-V	10.08.03.00159
Hose sleeve	ST G3/8-AG 13 MS-V	10.08.03.00160
Plug union, straight	STV-GE G3/8-AG 8	10.08.02.00237
Plug union, straight	STV-GE G3/8-AG 10	10.08.02.00252
Plug union, straight	STV-GE G3/8-AG 12	10.08.02.00209
Plug union, straight	STV-GE G3/8-AG 14	10.08.02.00211
Plug union, elbow	STV-W G3/8-AG 8	10.08.02.00236
Plug union, elbow	STV-W G3/8-AG 10	10.08.02.00255
Plug union, elbow	STV-W G3/8-AG 12	10.08.02.00163
Plug union, elbow	STV-WF G3/8-AG 8	10.08.02.00234
Plug union, elbow	STV-WF G3/8-AG 10	10.08.02.00259

