



HTR-UNI 1N G2 80

Holder HTR-UNI is delivered unassembled. The delivery consists of:

- Holder tube – available in various lengths
- Ball clamp – available in various versions


Available accessories: section adapter, tube adapter, tube adapter reducing set, suction cup connection

Technical data

Attribute	Value
Operating temperature	0 ... 80 °C
Length L1	80.00 mm
Suction cup connection	G1/4"-M
Cross-beam connection	1 nut slot

Design data

Attribute	Value
Length L1	80.00 mm
Length L2	70.00 mm
Length L	30.00 mm
Height H	27.50 mm
Outside diameter D	59.00 mm
Thread G1	G1/4"-M
Thread G2	M6-M
Thread length LG2	6.3 mm
Slewing angle W	15.0 °
Length L3	20.00 mm



Design data HTR-UNI 1N G2 80

Art.-Nr.: 10.01.03.00107

**Technical data**

Attribute	Value
Weight	170.0 g
Product family	HTR-UNI

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.03.00107

**Ordering Data Accessories 10.01.03.00107**

Typ		Item number
Sliding-bearing sleeve with collar	BUCHSE 32-25x21 PA	10.01.03.00097
Cross-beam connection	HTR-STB 30x30 UNI	10.01.03.00135
Cross-beam connection	HTR-STC D32 UNI	10.01.03.00108

