


Art.-Nr.: 10.01.03.00109



KGL G1/8-IG G1/8-AG A2

Ball joint KGL is delivered as a ready-to-connect product.



Design data KGL G1/8-IG G1/8-AG A2

Technical data

Attribute	Value
Material	Austenitic stainless steel
Height H	26.50 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-M

Design data

Attribute	Value
Height H	26.50 mm
Nominal diameter dn	2.00 mm
Thread G1	G1/8"-F
Thread length LG1	8.5 mm
Thread G2	G1/8"-M
Thread length LG2	7.0 mm
Key width SW1	14.0 mm
Slewing angle W	15.0 °

**Technical data**

Attribute	Value
Vertical load	300.0 N
Weight	26.0 g
Product family	KGL

Ball joint

KGL G1/8-IG G1/8-AG A2



Art.-Nr.: 10.01.03.00109



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.03.00109



Ordering Data Spare Parts 10.01.03.00109

Typ		Item number
Sealing ring (f. screwing)	DR G1/8 15/10x1.5 PA	10.07.08.00020



WWW.SCHMALZ.COM/10.01.03.00109