


Art.-Nr.: 10.01.03.00110

**Technical data**

Attribute	Value
Height H	37.50 mm
Thread G1	G1/4"-F
Thread G2	G1/4"-M

KGL G1/4-IG G1/4-AG

Ball joint KGL is delivered as a ready-to-connect product.

**Design data**

Attribute	Value
Height H	37.50 mm
Nominal diameter dn	3.50 mm
Thread G1	G1/4"-F
Thread length LG1	12.0 mm
Thread G2	G1/4"-M
Thread length LG2	10.0 mm
Key width SW1	19.0 mm
Slewing angle W	15.0 °

Design data KGL G1/4-IG G1/4-AG

**Technical data**

Attribute	Value
Vertical load	1,500.0 N
Weight	67.0 g
Product family	KGL



Ball joint

KGL G1/4-IG G1/4-AG



Art.-Nr.: 10.01.03.00110



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.03.00110



Ordering Data Spare Parts 10.01.03.00110

Typ		Item number
Sealing ring (f. screwing)	DR G1/4 18/13.5x1.5 PA	10.07.08.00021



WWW.SCHMALZ.COM/10.01.03.00110