


Art.-Nr.: 10.01.03.00111

**Technical data**

Attribute	Value
Height H	40.00 mm
Thread G1	G1/2"-F
Thread G2	G1/2"-M

KGL G1/2-IG G1/2-AG

Ball joint KGL is delivered as a ready-to-connect product.

**Design data**

Attribute	Value
Height H	40.00 mm
Nominal diameter dn	4.00 mm
Thread G1	G1/2"-F
Thread length LG1	14.0 mm
Thread G2	G1/2"-M
Thread length LG2	12.0 mm
Key width SW1	24.0 mm
Slewing angle W	15.0 °

Design data KGL G1/2-IG G1/2-AG

**Technical data**

Attribute	Value
Vertical load	2,500.0 N
Weight	116.0 g
Product family	KGL



Ball joint

KGL G1/2-IG G1/2-AG



Art.-Nr.: 10.01.03.00111



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.03.00111



Ordering Data Spare Parts 10.01.03.00111

Typ		Item number
Sealing ring (f. screwing)	DR G1/2 26/21.5x1.5 PA	10.07.08.00023



WWW.SCHMALZ.COM/10.01.03.00111