




HTR-UNI 2N FSTI

Holder HTR-UNI is delivered unassembled. The delivery consists of:

- Holder tube – available in various lengths
- Ball clamp – available in various versions

Available accessories: section adapter, tube adapter, tube adapter reducing set, suction cup connection



Design data HTR-UNI 2N FSTI

Technical data

Attribute	Value
Operating temperature	°C
Shape	for FSTI
Cross-beam connection	2 sliding block

Design data

Attribute	Value
Length L	28.00 mm
Width B	44.00 mm
Height H	27.50 mm
Outside diameter D	59.00 mm
Internal diameter d	18.00 mm
Thread G2	M6-M
Slewing angle W	15.0 °
Length L3	20.00 mm

Art.-Nr.: 10.01.03.00297

**Technical data**

Attribute	Value
Weight	155.0 g
Product family	HTR-UNI

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.03.00297**Ordering Data Accessories 10.01.03.00297**

Typ		Item number
Spring plunger	FSTI G1/4-AG G1/8-AG 25	10.01.02.00868
Spring plunger	FSTI G1/4-AG G1/8-AG 25 VG	10.01.02.00869
Spring plunger	FSTI G1/4-AG G1/8-AG 50	10.01.02.00992
Spring plunger	FSTI G1/4-AG G1/8-AG 50 VG	10.01.02.00993
Spring plunger	FSTI G1/4-AG G1/8-IG 25	10.01.02.00870
Spring plunger	FSTI G1/4-AG G1/8-IG 25 VG	10.01.02.00871
Spring plunger	FSTI G1/4-AG G1/8-IG 50	10.01.02.00994
Spring plunger	FSTI G1/4-AG G1/8-IG 50 VG	10.01.02.00995
Spring plunger	FSTI G3/8-AG G1/8-AG 25	10.01.02.00843
Spring plunger	FSTI G3/8-AG G1/8-AG 25 VG	10.01.02.00862
Spring plunger	FSTI G3/8-AG G1/8-AG 50	10.01.02.00996
Spring plunger	FSTI G3/8-AG G1/8-AG 50 VG	10.01.02.00997
Spring plunger	FSTI G3/8-AG G1/8-IG 25	10.01.02.00850
Spring plunger	FSTI G3/8-AG G1/8-IG 25 VG	10.01.02.00863
Spring plunger	FSTI G3/8-AG G1/8-IG 50	10.01.02.00998
Spring plunger	FSTI G3/8-AG G1/8-IG 50 VG	10.01.02.00999

