

Art.-Nr.: 10.01.03.00328



HTR-UNI 2N G2 110


Holder HTR-UNI is delivered unassembled. The delivery consists of:

- Holder tube – available in various lengths
- Ball clamp – available in various versions

Available accessories: section adapter, tube adapter, tube adapter reducing set, suction cup connection

Technical data

Attribute	Value
Operating temperature	0 ... 80 °C
Length L1	110.00 mm
Suction cup connection	G1/4"-M
Cross-beam connection	2 sliding block



Design data HTR-UNI 2N G2 110

Design data

Attribute	Value
Length L1	110.00 mm
Length L2	100.00 mm
Length L	30.00 mm
Width B	44.00 mm
Height H	27.50 mm
Outside diameter D	59.00 mm
Thread G1	G1/4"-M
Thread G2	M6-M
Thread length LG2	6.0 mm
Slewing angle W	15.0 °

Art.-Nr.: 10.01.03.00328

**Technical data**

Attribute	Value
Weight	204.2 g
Product family	HTR-UNI

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.03.00328**Ordering Data Accessories 10.01.03.00328**

Typ		Item number
Plug union, straight	STV-GE G1/4-AG 10	10.08.02.00251
Plug union, straight	STV-GE G1/4-AG 12	10.08.02.00208
Plug union, straight	STV-GE G1/4-AG 6	10.08.02.00205
Plug union, straight	STV-GE G1/4-AG 8	10.08.02.00207
Suction cup connection (rigid)	SAUG-ANB G1/4-AG 80	10.01.03.00292

**Ordering Data Spare Parts 10.01.03.00328**

Typ		Item number
Suction cup connection (rigid)	SAUG-ANB G1/4-AG 110	10.01.03.00327

