



SPLO 370x80 NBR-55

Çeşitli çaplarda ve isteğe bağlı olarak dokunmatik valfli olarak temin edilebilen vakum plakası SPLO, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	370 x 80
Yükseklik H	25.00 mm

Tasarım verileri

Attribute	Value
Yükseklik H	25.00 mm
Kafa uzunluğu Lk	344.90 mm
Yay stroku Z	7.5 mm
Uzunluk L3	338.00 mm
Genişlik B3	45.00 mm
Vantuz genişliği Bs	79.40 mm
Ls	372.40 mm
Lmaks.(S)	376.00 mm
Bmax(S)	86.00 mm
Bk	53.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPLO 370x80 NBR-55

Vakum plakası (oval)

SPLO 370x80 NBR-55



Art.-Nr.: 10.01.05.00006



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	100.0 mm
Emme kuvveti (-600mbar)	1270.00 N
Ağırlık	1200.0 g
Boyutlar (LxW)	370 x 80
Cilt	194.236 cm ³
Körük Sayısı	0.0
Ürün ailesi	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00006



WWW.SCHMALZ.COM/10.01.05.00006