

Düz vantuz (oval)

SGO 18x6 NBR-55 N021




Art.-Nr.: 10.01.05.00072



SGO 18x6 NBR-55 N021

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	18 x 6



Tasarım verileri SGO 18x6 NBR-55 N021

Tasarım verileri

Attribute	Value
Yükseklik H2	3.00 mm
Yükseklik H	12.00 mm
Kafa çapı Dk	8.5 mm
Nominal çap dn	1.50 mm
İç çap d1	6.0 mm
İç çap d	4.50 mm
Yay stroku Z	0.8 mm
Yükseklik H3	5.50 mm
Vantuz genişliği Bs	5.60 mm
Ls	17.60 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.05.00072

Düz vantuz (oval)

SGO 18x6 NBR-55 N021



Art.-Nr.: 10.01.05.00072



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	4.50 N
Ağırlık	0.5 g
Boyutlar (LxW)	18 x 6
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00072



Veri aksesuarları sipariş edin 10.01.05.00072

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N021 M5-AG DN200
Vantuz bağlantı nipel	SA-NIP N021 M5-IG DN200



WWW.SCHMALZ.COM/10.01.05.00072