

Flat suction cup (oval)

SGO 45x15 NBR-55 N023


Art.-Nr.: 10.01.05.00153



SGO 45x15 NBR-55 N023

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Dimension (LxW)	45 x 15



Design data SGO 45x15 NBR-55 N023

Design data

Attribute	Value
Height H2	8.00 mm
Height H	21.00 mm
Head diameter Dk	15.5 mm
Nominal diameter dn	3.00 mm
Internal diameter d1	13.0 mm
Internal diameter d	11.50 mm
Spring stroke Z	2.0 mm
Height H3	10.00 mm
Suction cup width Bs	14.40 mm
Ls	44.40 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.05.00153

Art.-Nr.: 10.01.05.00153

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Suction force (-600mbar)	28.20 N
Weight	6.3 g
Dimension (LxW)	45 x 15
Product family	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00153

**Ordering Data Accessories 10.01.05.00153**

Typ		Item number
Suction cup connection nipple	SA-NIP N023 G1/4-AG DN350	10.01.05.00122
Suction cup connection nipple	SA-NIP N023 G1/4-IG DN350	10.01.05.00121

