

Düz vantuz (oval)

SGO 60x20 NBR-55 N023




Art.-Nr.: 10.01.05.00154



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyutlar (LxW)	60x20

SGO 60x20 NBR-55 N023



Tasarım verileri

Attribute	Value
Yükseklik H2	8,00 mm
Yükseklik H	21,00 mm
Kafa çapı Dk	15,5 mm
Nominal çap dn	4,00 mm
İç çap d1	13,0 mm
İç çap d	11,50 mm
Yay stroku Z	2,5 mm
Yükseklik H3	10,00 mm
Vantuz genişliği Bs	19,00 mm
Ls	59,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 60x20 NBR-55 N023



WWW.SCHMALZ.COM/10.01.05.00154

Düz vantuz (oval)

SGO 60x20 NBR-55 N023



Art.-Nr.: 10.01.05.00154



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Emme kuvveti (-600mbar)	50,10 N
Ağırlık	9,70 g
Ürün ailesi	SGO
Boyutlar (LxW)	60x20

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00154



Sipariş Verisi Aksesuarlar 10.01.05.00154

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N023 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N023 G1/4-IG DN350



WWW.SCHMALZ.COM/10.01.05.00154